

DocuPrint P505 d A4 Monochrome Printer

Reliable Performer for Busy Workgroups



Delivering exceptional speed and quality in an amazingly compact unit

The Fuji Xerox DocuPrint P505 d is a reliable print solution that delivers high speed and quality monochrome printing that will meet the demands of any organisation. With simple operation and secure connectivity, it has all the features to enhance your workflow.

SPEED YOU NEED, DELIVERY YOU CAN RELY ON

You can't afford to wait for your prints, and with a blistering 63 pages per minute maximum output, the DocuPrint P505 d delivers the speed your workgroup requires, every time.

- Ultra-fast Print Speeds at 63 pages per minute, with first page out time of less than 4.6 seconds.
- High maximum monthly duty cycles of up to 215,000 pages per month to handle high document printing usage.

SMALL FOOTPRINT

The Fuji Xerox DocuPrint P505 d is packed with features, delivering higher productivity and better operations. All wrapped up in a small footprint, that helps save valuable office space.



DOCUPRINT P505 D QUICK FACTS

- Print up to 63ppm
- Print resolution of 1200 x 1200 dpi
- USB 3.0, Network ready, Optional Wireless Network
- Standard 550 sheet feeder + 150 sheet bypass tray
- 427.4 x 465.5 x 443.4 mm





Simple control, quality printing, customised for your needs.

Cutting edge functionality and performance meets an intuitive, customisable touch screen display – giving you complete control at the touch of a button.

CONSISTENT MONOCHROME PRINT QUALITY

The Fuji Xerox DocuPrint P505 d delivers high quality monochrome printing on every project. Engineered to meet the print requirements of high-volume production environments, it produces consistent quality throughout, so no matter how large the print run, you can be confident that the last page will look as good as the first.

The Fuji Xerox DocuPrint P505 d features CCSLED (Current Confinement Self-Scanning Light Emitting Device) technology that ensures high-resolution output at 1200 x 1200 dpi quality, whilst staying compact and achieving power-saving benefits.

ULTRA FAST DUPLEX SPEED WITH TRI-ROLL TECHNOLOGY

The Fuji Xerox DocuPrint P505 d incorporates a newly-developed 3 roller paper feed system, or 'tri-roll' system, that significantly increases duplex print speed by up to 88% of simplex print speed. It works by feeding an extra sheet of paper into the printer whilst the first 2 sheets are crossing over the tri-roll system. This advancement in operation increases productivity, and saves you money.

CUSTOMISABLE 5" TOUCH PANEL

Meet the industry's most advanced colour touchscreen interface. The 5-inch touchscreen, offers a user experience that sets a higher standard for customisation, personalisation and versatility.

With a familiar 'mobile' experience and support for task-focused apps, the DocuPrint P505 d allow you to view your print jobs faster and in less steps. These same features also allow you to print more quickly from your USB memory via one touch of the icon.

A highly intuitive layout guides you through every task from start to finish, placing critical functions near the top of the screen, and commonly used options front and centre. If you don't like where a function or icon is located? Customise the layout to make it yours.

This unmatched balance of hardware technology and software capability helps everyone who interacts with the DocuPrint P505 d, get more work done, faster.



Fast, simple and secure access to our connected world.

Print from almost any device quickly, simply and effectively, with secure, easy to use connection through both wired and wireless solutions all within our easy to use control system.

GIGABIT ETHERNET

Leveraging the huge bandwidth of Gigabit Ethernet, the DocuPrint P505 d provides a seamless printing solution that leverages the usability and performance of native applications to deliver a fast, accurate print solution that integrates into the creative workflow.

OPTIONAL WIFI AND WIFI DIRECT

WiFi capability enables easy network connection, providing secure, reliable operation from any network device.

With Optional WiFi Direct, all of your devices can connect directly to the printer quickly, securely and easily without the need for a wireless access point, ensuring fast, easy operation in any situation.

NFC ENABLED (TOUCH AND PRINT)

Using the latest Near Field Communication (NFC) technology, users can print from similarly enabled mobile devices simply and with minimal setup. Simply touch the device to the printer and a connection is made enabling fast and easy printing.

USB 3.0

Connect directly through the superfast USB 3.0 socket for ultimate in reliability and speed. Simple setup, whether using a Windows PC or Mac, delivering direct printing from within your productivity software environment directly, ensuring perfect reproduction and the fastest time to print possible.

SECURE, RELIABLE WORKGROUP PRINTING


With complete secure printing, including print on release, security and confidentiality can be maintained through any workflow, for a true end-to-end fully secure process.

STATE OF THE ART SECURITY STANDARDS

To protect sensitive information, data is encrypted and sent over networks using SSL/TLS and IPsec data encryption. An added line of digital defence is provided through SNMPv3 management software allowing you to monitor the status of your networked devices.

CONFIDENTIAL PRINTING

Through the SecurePrint service, users decide when their print run occurs, ensuring that documents can be printed confidentially and securely as needed without sacrificing the efficiency of the print queue.



Safeguard your assets, giving you more control over your print costs.

The Fuji Xerox DocuPrint P505 d is equipped with built-in solutions for ease of use and simple cost management features.

CENTREWARE INTERNET SERVICES

CentreWare Internet Services (CWIS) is a built-in management software, allowing administrators to monitor, configure, and troubleshoot network printers from their web browser. Configurable hotlinks provide convenient, point-of-need access to product information, software drivers, help-desk and customer support.


The software also generates email alerts that notify of events that require attention, such as low toner levels allowing easier management.

XEROX® STANDARD ACCOUNTING

Xerox® Standard Accounting (XSA) monitors not only the document pages your office produces but also who has produced them.

It allows you to easily manage access, gather data for print usage and cut costs by identifying excess expenses.

Xerox® Standard Accounting also gives you a simple yet effective way to enhance network security, by limiting access and tracking use of your printer.



CentreWare Internet Services



Xerox® Standard Accounting

Robust flexible options suited to your needs.

With the versatility and scalability to grow with your business the DocuPrint P505 d will optimise your office productivity and make your documents stand out with professional finishing options.



1 500-sheet output tray with tray-full sensor

2 Optional 250 GB Hard Drive Extension Kit increases the capabilities of numerous app-based functions.

3 A front-side USB port* allows users to quickly print from or any standard USB memory device.

4 150-sheet Bypass Tray handles media sizes from 76.2 x 127 mm to 215.9 x 355.6 mm

5 Tray 1 handles up to 550 sheets with custom sizes of 76.2 x 190.5 mm to 215.9 x 355.6 mm

6 The optional Stand (includes Caster) provides storage for toner cartridges and other supplies.

7 The High Capacity Feeder (includes Caster) adds up to 2,000 sheets with standard A4 and Letter size.

8 Add up to 4 additional 550-sheet paper trays that handle sizes from 76.2 x 215.9 mm to 190.5 x 355.6 mm (maximum of 2 additional trays with optional cabinet, maximum of 1 additional tray with High Capacity Feeder).

9 The optional finisher collates and staples sets of up to 50 sheets and includes a 500-sheet output tray.

10 The optional mailbox includes 4 bins and each tray can handle up to 100 sheets.

* USB ports can be disabled

Enjoy real savings for your business.

Outstanding print quality combined with some of the lowest running costs in the market.

SAVE WITH SUPER EA-ECO TONER

Super EA-Eco Toner contains a new polyester resin that dramatically effects the viscosity of the toner when changing temperature. This enables Super EA-Eco Toner to achieve 10-15°C lower fusing temperature than standard toner, reducing power consumption by up to 20%, and reducing CO₂ emissions by up to 35%. That means bigger savings for you and a greener planet for us all.

HIGH YIELD, LOWER COSTS

High-yield toner cartridges allow longer periods of uninterrupted productivity, reducing your total cost of operation.



Specifications of DocuPrint P505 d

| | | |
|--|--|--|
| Product Name | | DocuPrint P505 d |
| Print Speed | | Up to 63 ppm (A4) |
| Duplex Print Speed | | Up to 56 ppm (A4) |
| Print Resolution | | 1,200 x 1,200 dpi (Fuji Xerox Imaging Technology) |
| First-page-out-time | | Less than 4.6 seconds |
| Maximum Duty Cycle | | 215,000 pages/month |
| Memory (Standard) | | 2GB |
| Processor | | Dual Core 1.05GHz |
| PDL | | TIFF, FX PDF, PCL6, PCL5c, PS, XPS (XML Paper Specification) |
| Protocol | | Ethernet (standard): TCP/IP (IPv4/IPv6, LPD, IPP, IPPS, SMB, Port9100, WSD*, HTTP, HTTPS, SMTP, RARP, AutoIP, WINS, Telnet), SNMP, DHCP, BOOTP, Bonjour (mDNS), LDAP, LDAPS, Kerberos, DNS, DDNS, SNTTP, FTP IEEE 802.11b/802.11g/802.11n * WSD stands for Web Services on Devices. |
| Connectivity | | Ethernet (1000BASE-T/100BASE-TX/10BASE-T), USB 3.0 (Hi-Speed), Near Field Communication (NFC), Optional Wireless (IEEE802.11b/802.11g/802.11n) |
| Supported OS | | PCL Driver: Windows 10 (32bit), Windows 10 (64bit), Windows 8.1 (32bit), Windows 8.1 (64bit), Windows 7 (32bit), Windows 7 (64bit), Windows Server 2016 (64bit), Windows Server 2012 R2 (64bit), Windows Server 2012 (64bit), Windows Server 2008 R2 (64bit), Windows Server 2008 (32bit), Windows Server 2008 (64bit) Adobe® PostScript® 3™ Driver: Windows 10 (32bit), Windows 10 (64bit), Windows 8.1 (32bit), Windows 8.1 (64bit), Windows 7 (32bit), Windows 7 (64bit), Windows Server 2016 (64bit), Windows Server 2012 R2 (64bit), Windows Server 2012 (64bit), Windows Server 2008 R2 (64bit), Windows Server 2008 (32bit), Windows Server 2008 (64bit), macOS 10.12 Sierra, OS X 10.11 El Capitan, OS X 10.10 Yosemite, OS X 10.9 Mavericks, OS X 10.8 Mountain Lion, Citrix Xen App 6.0/ 6.5/ 7.5/ 7.6/ 7.7/ 7.8/ 7.9/ 7.11 |
| Input Paper Size | Standard Tray | A4, B5 (JIS), A5, Legal 14", Legal 13", Letter, Executive Custom size (Width: 76.2 mm to 215.9 mm, Length: 190.5 mm to 355.6 mm) |
| | Multi-Purpose Tray | Width: 76.2 to 215.9mm |
| | | Length: 127 to 355.6mm |
| | Optional 550-sheet Feeder | Width: 76.2 to 215.9mm Length: 190.5 to 355.6mm |
| | Optional 2000-sheet High Capacity Feeder (HCF) | A4, Letter Width: 139.7 to 215.9mm Length: 203.2 to 355.6mm |
| 2 Sided Print – Custom Size | | |
| Input Paper Weight | | All trays (except HCF & Duplex): 60 to 220gsm, HCF & Duplex: 60 to 176gsm |
| Media Input Capacity | | Bypass Tray: 150 sheets; Standard Tray: 550 sheets Optional Feeder: 550 sheets; Optional High-Capacity Feeder: 2,000 sheets; Maximum: 3,250 sheets |
| Media Output Capacity | | Standard Output: 500 sheets face-down Optional Finisher: 500 sheets face-down Optional 4-bin Mailbox: 100 sheets face-down x 4 |
| Dimensions (WxDxH) | | 427.4 x 465.5 x 443.4 mm |
| Weight (with toner cartridges) | | 22.3 kg |
| Power Support | | AC 110-127 V ± 10%, 12A, 50/60Hz ± 3% AC 220-240 V ± 10%, 8A, 50/60Hz ± 3% |
| Power Consumption | | AC 115V: Maximum power consumption: 1230 W Sleep mode: 0.9 W or less AC 230V: Maximum power consumption: 1200 W Sleep mode: 1.1 W or less |
| Noise Level | | During operation (main unit only): 7.50 B; 59.5 dB(A) During stand-by (main unit only): 5.80 B; 39.4 dB(A) |
| Accessories | | Order Number |
| 550 Sheet Feeder | | EC103493 |
| High Capacity Feeder (2,000 pages) | | EC103494 |
| Caster | | EC103495 |
| Cabinet | | EC103496 |
| HDD extension Kit | | EC103497 |
| Wireless LAN Kit | | EC103438 |
| 4-Bin Mailbox | | EC103499 |
| Finisher | | EC103500 |
| Consumables* | | Page Yield Order Number |
| Black Standard Toner Cartridge | | 12,000 CT203069 |
| Black High Capacity Toner Cartridge | | 30,000 CT203070 |
| Black Drum Cartridge | | 60,000 CT351157 |
| Paper Roller Kit | | 100,000 EC103505 |
| Fusing Unit 110V | | 200,000 EC103506 |
| Fusing Unit 220V | | 200,000 EC103507 |
| BTR (Bias Transfer Roll) | | 200,000 EC103508 |
| Staple Cartridge Types XE (5,000 x 2pcs) | | - CWAA0856 |

*Declared yield in accordance with ISO/IEC 19752. Yield may vary depending on image, area, coverage and print mode (job length, media size, media type and orientation). Printer is shipped with one set of starter toner cartridge with average yield of 10,000 pages and up to 60,000 pages for drum cartridges.



The available model varies depending on the country/region. Please ask the sales representatives for details.

Reproduction Prohibitions Please note that reproduction of the following is prohibited by law: Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. Unused postage stamps, post cards, etc. Certificate stamps stipulated by law. Reproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

For Your Safety

⚠ Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection. Otherwise, electronic shock may result in the case of a failure or short circuit.

For more information or detailed product specification, please call or visit us at

Fuji Xerox (Hong Kong) Limited

11/F Cityplaza 4, 12 Taikoo Wan Road, Quarry Bay, Hong Kong
Tel. 852-2513-2513

<https://www.fujixerox.com.hk/>

