

Versant 180i Press Functions & Specifications

Options cannot be listed in the brochure are listed.

2nd High Capacity Feeder C1-DS (Optional)

Item	Description
Paper Size ^{*1}	Standard size: Max A3, 11 x 17", Min A6 Custom size: 98 x 148 mm to 330 x 488 mm
Paper Weight	52 to 350 gsm
Feeding Capacity / Number of Tray ^{*2}	2000 sheets x 2-tray
Power Supply	AC100-120 V +/- 10 %, 5 A, AC220-240 V +/- 10 %, 3 A, 50/60 Hz common
Maximum Power Consumption	660 W
Dimensions	W 988 x D 762 x H 992 mm
Weight	235 kg

Note: Use this option connected with High Capacity Feeder C3-DS.

Note: When 2nd High Capacity Feeder C1-DS is connected, the optional Multi Sheet Inserter for Banner Print is detached from the printer and attached to this option.

*1: When setting main scanning 98 to 182 mm paper, Post Card Kit is required.

*2: 90 gsm paper.

Chained Air Suction Feeder C1-DS / C1-DSXL (Optional)

Item	Chained Air Suction Feeder	
	C1-DS-R + C1-DS-L ^{*1}	C1-DS-R + C1-DSXL-L ^{*2}
Paper Size ^{*3}	Standard size: Max A3, 11 x 17", Min A6 Custom size: 98 x 148 mm to 330 x 488 mm	
Paper Weight	52 to 400 gsm ^{*5}	
Feeding Capacity / Number of Tray ^{*6}	2100 sheets x 2-tray x 2-connection	2100 sheets x 2-tray + 800 sheets ^{*7} + 2100 sheets
Power Supply	AC100-120 V +/- 10 %, 6 A, AC220-240 V +/- 10 %, 4 A, 50/60 Hz common x 2 power	
Maximum Power Consumption	880 W x 2 power	
Dimensions	W 1980 x D 762 x H 992 mm	W 2572 x D 762 x H 992 mm ^{*8}
Weight ^{*9}	403 kg	421 kg ^{*8}

Note: Multi Sheet Inserter for Banner Print is included.

Note: Chained Air Suction Feeder C1-DSXL-L can feed long paper only from the Upper tray.

*1: C1-DS-R and C1-DS-L are required as a set.

*2: C1-DS-R, C1-DSXL-L and Banner Unit for Air Suction Feeder C1-DSXL are required as a set.

*3: When setting main scanning 98 to 182 mm paper, Post Card Kit is required.

*4: Duplex Automatic Print supports paper size up to 330 x 864 mm.

*5: For long paper from 330 x 488 mm to 330 x 660 mm: 52 to 350 gsm; for paper up to 330 x 864 mm: 52 to 300 gsm; for paper up to 330 x 1200 mm: 52 to 256 gsm. Duplex Automatic Print supports paper weight up to 220 gsm.

*6: 90 gsm paper.

*7: 100 sheets for paper longer than 864 mm (90 gsm).

*8: The optional Banner Unit for Air Suction Feeder C1-DSXL is included.

*9: Including Multi Sheet Inserter for Banner Print and Large Size UI panel.

Folder Unit CD1 / CD2 (Optional)

Item	Description	
	Folder Unit CD1	Folder Unit CD2
Z Fold Half Sheet	Paper Size	A3, JIS B4
	Paper Weight	60 to 90 gsm
Tri-fold	Paper Size	A4
	Paper Weight	60 to 90 gsm
	Paper Capacity*	30 sheets
Power Supply	AC100-127 V +/- 10 %, 1 A, AC200-240 V +/- 10 %, 0.6 A, 50/60 Hz common	
Maximum Power Consumption	120 W	
Dimensions	W 232 x D 726 x H 992 mm	W 235 x D 725 x H 992 mm
Weight	53 kg	55 kg

Note: Folder Unit CD1 is option for C3 Finisher and C3 Finisher with Booklet Maker.

Note: Folder Unit CD2 is option for Finisher D6, Finisher D6 Plus and Finisher D6 with Booklet Maker.

*: 82 gsm paper.

High Capacity Stacker A1 (Optional)

Item	Description	
Paper Capacity ¹	Output Tray ²	500 sheets ³
	High Capacity Stacker – Stacker Cart	5000 sheets
Paper Size	Output Tray	Standard size: Max A3, Min A6 Custom size: 98 x 148 mm to 330 x 1200 mm
	High Capacity Stacker – Stacker Cart	Standard size: Max A3, Min JIS B5 Custom size: 203 x 182 mm to 330 x 488 mm
Paper Weight	Output Tray	52 to 400 gsm
	High Capacity Stacker – Stacker Cart	52 to 300 gsm
Power Supply	AC100-240 V +/- 10 %, 1.5 A (100 V) / 0.8 A (240 V), 50/60 Hz common	
Maximum Power Consumption	192 W	
Dimensions	W 800 x D 725 x H 1042 mm	
Weight ⁴	155 kg	

Note: Interface Decurler Module D1 is required.

*1: 80 gsm paper.

*2: For paper longer than 330 x 488 mm, the capacity is not guaranteed. When the optional Banner Print Extension Kit is installed, 100 sheets of long paper up to 330 x 864 mm; 10 sheets of long paper up to 330 x 1200 mm can be stacked.

*3: When the optional Banner Print Extension Kit is installed, 250 sheets.

*4: Including Stacker Cart.

Interface Decurler Module D1 / Interface Decurler Module (ILS) (Optional)

Item	Description	
	Interface Decurler Module D1	Interface Decurler Module (ILS)
Power Supply	AC100-240 V +/- 10 %, 2.5 A (100 V) / 1 A (240 V), 50/60 Hz common	AC100-240 V +/- 10 %, 3 A (100 V) / 1.5 A (240 V), 50/60 Hz common
Maximum Power Consumption	250 W	360 W
Dimensions	W 340 x D 725 x H 992 mm	
Weight	40 kg	47 kg

Note: Interface Decurler Module D1 or Interface Decurler Module (ILS) is necessary for connecting Finisher D6, Finisher D6 Plus, Finisher D6 with Booklet Maker or High Capacity Stacker A1 to the printer. Performance Package option requires Interface Decurler Module (ILS).

Crease / Two-sided Trimmer D2 (Optional)

Item		Description
Two-sided Trim	Paper Size	Standard size: Max A3, Min A4 Custom size: 194 x 210 mm to 330 x 488 mm
	Paper Weight	52 to 350 gsm
	Trim dimensions	One side: 6 to 25 mm
Crease	Paper Size	Standard size: Max A3, Min JIS B5 Custom size: 182 x 210 mm to 330 x 488 mm
	Paper Weight ^{*1}	60 to 350 gsm
	Number of lines ^{*2}	1 to 5
Power Supply		AC100-240 V +/- 10 %, 4 A (100 V) / 2 A (240 V), 50/60 Hz common
Maximum Power Consumption		480 W
Dimensions		W 605 x D 725 x H 992 mm
Weight		128 kg

Note: Finisher D6, Finisher D6 Plus or Finisher D6 with Booklet Maker is required.

*1: When using the booklet finishing. 157 gsm or more is supported for single sheet.

*2: The continuous print speed will decrease significantly as the number of lines increases.

SquareFold Trimmer D1 (Optional)

Item		Description
Paper Size		Same as the paper size of the Finisher D6 Booklet Finishing.
Paper Weight		Same as the paper weight of the Finisher D6 Booklet Finishing.
Booklet Tray Capacity ^{*1}		20 sets (15 sheets bind and below), 15 sets (16 sheets bind and above)
Face Trim	Capacity ^{*2}	Saddle Staple: 30 sheets, Single Fold: 5 sheets
	Trim dimensions	2 to 20 mm

Item	Description
Square Fold Capacity ^{*2*3}	30 sheets
Power Supply	AC100-240 V +/- 10 %, 0.8 A (100 V) / 0.4 A (240 V), 50/60 Hz common
Maximum Power Consumption	96 W
Dimensions	W 1066 x D 725 x H 552 mm
Weight	100 kg

Note: Finisher D6 with Booklet Maker is required.

*1: Paper may not be accepted depending on paper type and other usage conditions.

*2: The capacity can decrease depending on type and weight of paper being used and other conditions.

*3: Square folding is not supported for single-folding and saddle stapling of less than 5 sheets.

Insertor D1 (Optional)

Item	Description
Paper Size	Standard size: Max A3, Min A5 Custom size: 182 x 148 mm to 330 x 488 mm
Paper Weight	52 to 350 gsm
Paper Capacity ^{*1}	250 sheets
Power Supply	Supplied from Interface Decurler Module D1 or Interface Decurler Module (ILS)
Dimensions	W 700 ^{*2} x D 725 x H 1235 mm
Weight	45 kg

Note: Finisher D6, Finisher D6 Plus, Finisher D6 with Booklet Maker or High Capacity Stacker A1 is required.

*1: 82 gsm paper.

*2: The width of the paper transfer part only when connected to the device is 165 mm.

Finishing Transport (Optional)

Item	Description
Power Supply	AC100-240 V +/- 10 %, 5 A (100 V) / 2 A (240 V), 50/60 Hz common
Maximum Power Consumption	500 W
Dimensions	W 593 x D 652 x H 1004 mm
Weight	65 kg

Note: Finishing Transport and Finisher D6 Plus are required for connecting a third party vendor finisher to the printer.

Notes

- 1) To comply with paper weight specifications, it is recommended to use Fuji Xerox recommended paper.
Document may not be printed correctly depending on usage conditions.
- 2) Functional spare parts will be available for at least 7 years after the product is no longer manufactured.