

# Versant 3100i Press Functions & Specifications

Options cannot be listed in the brochure are listed.

## 2nd High Capacity Feeder C1-DS (Optional)

Item	Description
Paper Size <sup>*1</sup>	Standard size: Max A3, 11 x 17", Min A6 Custom size: 98 x 148 mm to 330 x 488 mm
Paper Weight	52 to 350 gsm
Feeding Capacity / Number of Tray <sup>*2</sup>	2000 sheets x 2-tray
Power Supply	AC100-120 V +/- 10 %, 5 A, AC220-240 V +/- 10 %, 3 A, 50/60 Hz common
Maximum Power Consumption	660 W
Dimensions	W 988 x D 762 x H 992 mm
Weight	235 kg

Note: Use this option connected with High Capacity Feeder C3-DS.

Note: When 2nd High Capacity Feeder C1-DS is connected, the optional Multi Sheet Inserter for Banner Print is detached from the printer and attached to this option.

\*1: When setting main scanning 98 to 182 mm paper, Post Card Kit is required.

\*2: 90 gsm paper.

## Chained Air Suction Feeder C1-DS / C1-DSXL (Optional)

Item	Chained Air Suction Feeder	
	C1-DS-R + C1-DS-L <sup>*1</sup>	C1-DS-R + C1-DSXL-L <sup>*2</sup>
Paper Size <sup>*3</sup>	Standard size: Max A3, 11 x 17", Min A6 Custom size: 98 x 148 mm to 330 x 488 mm	
Paper Weight	52 to 400 gsm <sup>*5</sup>	
Feeding Capacity / Number of Tray <sup>*6</sup>	2100 sheets x 2-tray x 2-connection	2100 sheets x 2-tray + 800 sheets <sup>*7</sup> + 2100 sheets
Power Supply	AC100-120 V +/- 10 %, 6 A, AC220-240 V +/- 10 %, 4 A, 50/60 Hz common x 2 power	
Maximum Power Consumption	880 W x 2 power	
Dimensions	W 1980 x D 762 x H 992 mm	W 2572 x D 762 x H 992 mm <sup>*8</sup>
Weight <sup>*9</sup>	403 kg	421 kg <sup>*8</sup>

Note: Multi Sheet Inserter for Banner Print is included.

Note: Chained Air Suction Feeder C1-DSXL-L can feed long paper only from the Upper tray.

\*1: C1-DS-R and C1-DS-L are required as a set.

\*2: C1-DS-R, C1-DSXL-L and Banner Unit for Air Suction Feeder C1-DSXL are required as a set.

\*3: When setting main scanning 98 to 182 mm paper, Post Card Kit is required.

\*4: Duplex Automatic Print supports paper size up to 330 x 864 mm.

- \*5: For long paper from 330 x 488 mm to 330 x 660 mm: 52 to 350 gsm; for paper up to 330 x 864 mm: 52 to 300 gsm; for paper up to 330 x 1200 mm: 52 to 256 gsm. Duplex Automatic Print supports paper weight up to 300 gsm.
- \*6: 90 gsm paper.
- \*7: 100 sheets for paper longer than 864 mm (90 gsm).
- \*8: The optional Banner Unit for Air Suction Feeder C1-DSXL is included.
- \*9: Including Multi Sheet Inserter for Banner Print.

**Notes**

- 1) To comply with paper weight specifications, it is recommended to use Fuji Xerox recommended paper.  
Document may not be printed correctly depending on usage conditions.
- 2) Functional spare parts will be available for at least 7 years after the product is no longer manufactured.