

## EX C9065 / C9070

## Print Server Powered by Fiery®

Do more complex and higher value jobs with the high performance of the EX C9065 / C9070 Print Server for the PrimeLink™ C9070 / C9065 Printer.

**Boost Your Production And Profits**

Easily handle heavy workloads and provide faster turnaround times. Support for industry-leading variable data printing (VDP) formats such as PDF/VT, PPML, VPS and VIPP allow PSPs to satisfy customer demands and meet tight deadlines.

**Print Perfect PDFS.**

By supporting the Adobe® PDF Print Engine®, Fiery® servers offer a native end-to-end PDF workflow, allowing you to improve the consistency of your printed output from design to print.

**Reduce Errors And Waste.**

Avoid costly mistakes with the troubleshooting, preflight and proofing tools of the optional Fiery® Graphic Arts Package, Premium Edition.

**A Secure, Integrated Production Environment**

Built on the Microsoft Windows 10 platform, the EX C9065 / C9070 Print Server contains the latest security protections, such as Windows Defender. Other enhancements include encryption, secure printing, user authentication, and configurable backup and restore capabilities. The server features standard JDF connectivity.

**Speed Up Makeready.**

Easily perform complex document preparation using the intuitive Fiery® Impose-Compose.

**Turn Up The Impact With Personalisation.**

With Fiery® FreeForm™ Create, you can quickly and simply personalise existing files for free – with no additional VDP software required. Add variable elements such as text, images, or barcodes with just a few clicks.



# EX C9065 / C9070 Print Server Powered by Fiery®

## Fiery Driven™ Engines

- PrimeLink C9070 / C9065 Printer
- Supports all engine finishing devices

## Platform

- Fiery® FS350 Pro software
- Server touchscreen interface for easy device management and status information with Fiery® QuickTouch™ software

## Fiery® Colour Technology

- Fiery® Spot-On™
- PANTONE® Colour Enabled
- Composite Overprint of grayscale, spot and CMYK Colours
- Fiery® Image Enhance Visual Editor
- Calibration
  - Fiery® Calibrator
  - ColorCal (standard, off the glass)
  - EFI™ ES-2000 spectrophotometer (optional)
  - Job-based calibration integration
- Auto trapping
- Image smoothing
- Fiery® Graphic Arts Package, Premium Edition (optional)
  - Fiery® Spot Pro™
  - Fiery® ImageViewer
  - Fiery® Preflight and more

## Adobe® Interpreter Support

- CPSI version 3020
- Adobe® PDF Print Engine® 4\*1

## Productivity And Workflow

- Standard support for XLS media
- Bi-directional paper catalog management
- Fiery® Impose
- Fiery® Compose
- Spool-RIP-Print simultaneously
- Fiery® Command WorkStation®
- Advanced Job Management features include Schedule Print, Suspend on Mismatch, Job Reorder, Force Print, Process Next, Quick Doc Merge, Sequential Print and Rush Print
- Set Page Device mapping
- Pad printing
- Fiery® Hot Folders and Virtual Printers
- Support of PDF XObjects on a per-job basis
- Fiery® Driver
- Fiery® Remote Scan
- Fiery® Go (Android™ and iOS)

## Variable Data Printing (VDP)

- Supports the following formats: FreeFlow VI Compose, VIPP, PPML 2.0/2.2/3.0, Creo® VPS, PDF/VT-1 and PDF/VT-2
- VDP Record Range Printing
- Fiery® VDP imposition
- VDP Raster Preview
- VDP Resource Manager
- Fiery® FreeForm™ Create

## Network Environments

- JMF/JDF

## Security Features

- Secure erase

- Encryption of critical information
- Access controls
- Port blocking
- IP filtering
- IPsec network encryption
- Secure connections using HTTPs
- Secure Printing
- Digitally signed software updates
- Windows Defender SmartScreen
- Windows Data Execution Prevention (DEP)
- Windows Defender Antivirus
- PostScript® security

## EMC

- C-TICK (Australia and New Zealand)
- BSMI – Taiwan
- MSIP – Korea

## Safety

- CB Scheme
- BSMI – Taiwan

## Fiery® Options

- Fiery® Graphic Arts Package, Premium Edition
- Fiery® Color Profiler Suite\*2 with EFI™ ES-2000 spectrophotometer
- Fiery® NX Station GL: Fiery® work stand, Fiery® Ticker, 22" monitor, wireless keyboard and mouse
- Hard drive security option

## Integration

- FreeFlow Digital Workflow Collection
- Fiery® API
- Native Fiery® JDF

\*1: Updated with enhancements and service releases on an ongoing basis.

\*2: Free trial in demo mode

## Print Server [EX C9065 / C9070 Print Server Powered by Fiery®]

Item	Description
Type	External
CPU	Intel® Core™ i5-6500 Processor (3.2 up to 3.6 GHz with Turbo), Quad Core
Storage device	Hard disk: 1 TB, DVD-RW drive
Memory capacity	8 GB (Max: 8 GB)
Server Operation System	Windows 10 IoT Enterprise 2016 LTSB (64bit)
Page Description Language	Adobe® PostScript® Level 1, 2, Adobe® PostScript® 3™, Enhanced PCL6 / PCL 5 PDF/VT-1, PDF/VT-2, VIPP*1, PPML, VPS
Print Data Format	PDF/X-1a, 3 and 4 Adobe® Acrobat® XI: Native PDF 1.3, 1.4, 1.5, 1.6, 1.7 EPS, TIFF, TIFF/IT-P1, JPEG*2

Item	Description
Supported Operating System	Windows 10 (32 bit / 64 bit), Windows 8.1 (32 bit / 64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit), Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit), macOS 10.15 Catalina, 10.14 Mojave, 10.13 High Sierra, 10.12 Sierra, OS X 10.11 El Capitan
Interface	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T, USB3.0 x 7, USB2.0 x 2
Network Protocol	TCP/IP, AppleTalk*3, Bonjour, SNMP, Port 9100, IPP, FTP, SMB, WSD*4, Point and Print, Print via Email (PS/PDF), IPv6, LDAP
Power Supply	AC100-240 V +/- 10 %, 6 A (100 V) / 3 A (240 V), 50/60 Hz common
Maximum Power Consumption	0.4 kW
Dimensions	W 235 x D 464 x H 527 mm
Weight	16.5 kg

\*1: Used with optional software FreeFlow VI Compose. \*2: Only available with Fiery® Graphic Arts Package, Premium Edition.  
\*3: AppleTalk is not supported by Mac OS X 10.6 Snow Leopard or later. \*4: WSD stands for Web Services on Devices.

Adobe, Adobe logo, PostScript, PostScript logo and Adobe PDF are either registered trademarks or trademarks of Adobe in the United States and/or other countries. All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies. The product specifications, appearance and other details in this brochure are subject to change without notice for improvements. The available model varies depending on the country/region. Please ask the sales representatives for details.

# FUJIFILM

For more information or detailed product specifications, please call or visit us at

**FUJIFILM Business Innovation Hong Kong Limited**

11/F, 12 Taikoo Wan Road, Quarry Bay, Hong Kong  
Tel. 852-2513-2513

[fujifilm.com/fbhk](http://fujifilm.com/fbhk)

**FUJI XEROX** 

This catalog includes Fuji Xerox product(s), licensed from Xerox Corporation. The distributor of the product(s) is FUJIFILM Business Innovation Corp. Xerox, Xerox and Design, Fuji Xerox and Design as well as FreeFlow and PrimeLink are registered trademarks or trademarks of Xerox Corporation in Japan and/or other countries.

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

The information is as of April, 2021. PIC-0143 HK (2002-R1)